
Adapter Flange for butterfly flange AF 40 to AF 125



The asa suction unit is screwed to the asa adapter flange, which is welded to the tank. Due to low installation costs and compact design, purchasing as a suction units is cost effective. A switch (mechanical or inductive) can be mounted on the standard block for monitoring matters. The adapter flange may only be welded with demounted butterfly flange.



Technical Data

order number	description	Α	В	С	D	F	G	Н	J	K	weight
		[in]	[in]	[in]	[in]	[in]	[mm]	[in]	[in]	[in]	[lbs]
SDAET040KU00	adapter 40	4.33	1.93	0.98	5.12	0.55	M12 (4x)			3.50 ± 0.04	4.18
SDAET063KU00	adapter 50 & 63	4.92	2.48	0.98	5.91	0.63	M12 (4x)			4.06 ± 0.04	5.39
SDAET080KU00	adapter 80		3.23	0.98	5.91	0.55	M16 (4x)	2.44	4.19	4.29 ± 0.04	4.73
SDAET100KU00	adapter 100		4.06	0.98	7.09	0.55	M16 (4x)	3.06	5.12	5.47 ± 0.04	6.16
SDAET125KU00	adapter 125		5.04	0.98	8.07	0.55	M16 (4x)	3.62	6.00	6.46 ± 0.04	7.26

Material

flange material	steel 1.0037 or 1.0570				
al					

Fits On

М

SDAET040KU00	SDA0040U00, SDA00040W
SDAET063KU00	SDA0050U00, SDA0063U00, SDA00050W, SDA00063W
SDAET080KU00	SDA0080U00, SDA00080W
SDAET100KU00	SDA0100U00, SDA00100W
SDAET125KU00	SDA0125U00, SDA00125W

